



## AquaCatch skid unit



## AquaCatch control panel



# AquaCatch

The smart solution for press water recycling

## AquaCatch makes the press water recycling more efficient

- ◆ Dynamic control of press water recycling to maximize savings and always guarantee correct rinsing
- ◆ Press water can be automatically routed to different rinse zones or to the pre-wash depending on programs
- ◆ Optimum water recycling flows are defined according to color and washing process compatibility
- ◆ System can mix recycled water and fresh water to optimize the rinse quality
- ◆ Simple on-site configuration is possible through an intuitive graphic interface and touch screen display
- ◆ Measure of actual water recycled to increase transparency and continuously track savings
- ◆ Inductive flow meter integrated in the system
- ◆ Real-time alarms to prevent quality and production issues
- ◆ Automatic switch to fresh water when not enough press water is available
- ◆ Compact pre-assembled solution to reduce installation complexity and risks
- ◆ Increased efficiency and savings compared to traditional press water recycling solutions
- ◆ Designed for both Press Water Recycling (PWR) and Centrifuge Water Recycling (CWR)
- ◆ CE certified