



# Energy Optimizer *Plus*

The smart heat exchanger for laundry process water

## The most efficient heat exchanger for laundries...

- ◆ made entirely in stainless steel to handle the most difficult waste water
- ◆ technology based on rotating disks to enhance the heat transfer and avoid foiling
- ◆ efficiency proved by more than 1000 installations
- ◆ low maintenance required
- ◆ scalable to handle from 5 m<sup>3</sup>/h to 30 m<sup>3</sup>/h
- ◆ CE certified

## ... just became smarter

- ◆ monitoring of water temperature, pressure, flow and pH
- ◆ real-time alarms
- ◆ visualization of trends and KPIs
- ◆ calculation of actual energy recovered and savings
- ◆ possibility to export data (USB)
- ◆ possibility to automatically correct the pH of the waste water and adjust the water flow to maximize the energy recovery
- ◆ 7" touch screen display with a user friendly graphic interface
- ◆ multi-language and simple on-site customization
- ◆ all the components required for a correct installation are pre-assembled in the main unit