



for up to **8**  
wash extractors

# Turbo COMPACT Dispenser

## THE COMPACT DISPENSING SOLUTION FOR WASH EXTRACTORS

- ◆ Dosing system for up to 8 wash extractors and max 8 products
- ◆ Ecolab *myControl* PLC with touch screen display and data management functionalities
- ◆ Two integrated dosing pumps to increase dispensing capacity for bigger machines
- ◆ Compatible with Ecolab Turbo Pump (50L/h) and Elados Membrane Pump (54l/h)
- ◆ Integrated flow meter (Ecolab Oval Gear Meter) for precise metering
- ◆ PP fitting and PEX tubing
- ◆ Operating environment 5°C - 40°C, up to 90% humidity
- ◆ Protection class GFPP - IP44
- ◆ Resistant to chemicals with pH between 0.8 and 12.0
- ◆ Splash guard and drip tray
- ◆ Compliant with CE, RoHS II and WEEE requirements
- ◆ Reliable and compact complete dosing system
- ◆ Separate flush line to increase dispensing speed
- ◆ Flush controlled by the flow meter to avoid mix of different products
- ◆ High flexibility in the management of washing programs (up to 99 programs)
- ◆ Dimensions: 1550 mm x 1100 mm x 480 mm
- ◆ Wall adapters included in the installation kit